

Telephone Ringer Strobe Light



This unit automatically flashes when the telephone rings

- * Unit can be used with existing telephones
- * Unit can be used by the hearing impaired
- * Excellent for noisy environments
- * The strobe light operates for 5 seconds after the telephone stops ringing
- * The strobe light lenses are available in 5 colors: clear , red , blue , green and yellow
- * The unit can be plugged into any standard telephone jack
- * Unit is supplied with a 7' telephone cable & 12 volt power supply

TRSL-1

Manufactured By:
Lari-Jo Inc.

Web site: www.lari-jo.com E-mail: rap@lari-jo.com
611 Hall Street - Warren, Ohio 44483 Phone:330-392-6800 Fax:330-393-9301